





TYP 133




16 4




8 4 4



12 10 10 1



5-7 10 1 1 3 6 12




8 8



5 1 1 2 4

ISM-FLA-15



Colli	Ersatzteil Nummer	Dimension
Colli 1/2	FLA.211	602x372x22
	FLA.212	602x352x16
	FLA.304 x3	567x315x16
	FLA.403	568x324x16
	FLA.906 x2	300x95x16
	FLA.907	532x95x16




Colli	Ersatzteil Nummer	Dimension
Colli 2/2	FLA.112	1962x352x16
	FLA.113	1962x352x16
	FLA.607	1971x577x2.5
	FLA.711	1256x596x16
	FLA.712	713x596x16
	FLA.803	1142x482x4









FLA.304



FLA.403

1








$\varnothing 8 \times 30 \text{mm}$  A 12	$\varnothing 15 / 12 \text{mm}$  C 8	L=20mm  D2 4
--	---	---



2




3





	+4.0x16mm	6.5x48x16		+8x30mm
T3	P1	F22	O1	A
3	3	4	1	4


4




5






6








7









8


6,4 x 50mm 		
B	O	E1
4	1	4













9

	+3.0x20mm 
L	P7
10	5-7








	#4.0x16mm
O1	P1
1	3

















	±3.5x13mm	±5.0x60mm	±10x50mm
L19	P5	P12	O7
1	2	1	1



±5/16mm		
	J3	E
12		8










	3.0x16mm 
J8	P11
10	10



 HG 5	 P5 10
---	--



M4x22mm	
	
U	S
4	2

